



PRODUCT-DETAILS

BVBD-P299GT

COND FTNG 90DCURV PG29 NW29 IP66BLK



General Information

Extended Product Type:	BVBD-P299GT
Product ID:	7TAA292150R0103
EAN:	7630030217432
Catalog Description:	COND FTNG 90DCURV PG29 NW29 IP66BLK
Long Description:	VB Connector 90 Degree Curved Elbow, PG Thread, for IP66 Conduit - Thread PG 29, Fits to Conduit Size NW/Metric 29/32, Color Black
Display Name:	BVBD-P299GT

Additional Information

Product Main Type:	PMA Flexible Cable Protection
Application:	For Cable Protection Systems In a Wide Range of Applications
Product Type:	Fittings for Nylon Flexible Conduits

Ordering

EAN:	7630030217432
UPC:	786209948960

Technical

Number of Batteries:	0
Color:	Black
Material:	High-Grade Specially Formulated Polyamide/Nylon 6
Size:	PG29

Environmental

WEEE Category:	Product Not in WEEE Scope
-----------------------	---------------------------

Container Information

Package Level 1 Units:	20 EA
Package Level 1 EAN:	7630030217432
Package Level 1 Height:	0 mm 0 in
Package Level 1 Depth / Length:	0 mm 0 in
Package Level 1 Width:	0 mm 0 in

Certificates and Declarations

Data Sheet, Technical Information:	BVBD-P299GT
Instructions and Manuals:	BVBD-P299GT
Declaration of Conformity - CE:	9AKK107680A0674

External Classifications and Standards

ETIM 8:	EC001176 - Screw connection for corrugated plastic hose
ETIM 9:	EC001176 - Screw connection for corrugated plastic hose
UNSPSC:	39131717

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

