



Product data sheet

Power tools for trade & industry

Cordless Wood Nailer

PRO GNH 18V-35



Precise fastening with minimized recoil and maximum consistency

The most important data

Nail length	15 – 35 mm
Nail diameter	0.6 mm
Triggering system	Single sequential actuation + Full sequential actuation

Part Number 0 601 482 701

Technical data

Technical data

Collation angle	0 °
Nail diameter	0.6 mm
Nail length	15 – 35 mm
Nail/Staple type	Pin
Triggering system	Single sequential actuation + Full sequential actuation
Weight excl. battery	1.7 kg
Battery voltage	18.0 V
Magazine capacity	110 Pcs
Packaging dimensions (width x length x height)	360 x 444 x 151 mm
Compatible nails/staples	Bosch nails
BITURBO	No

Noise/vibration information

Total vibration values

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- No markings on workpiece thanks to reduced recoil and no-mar pads with different contact areas for various applications
- Perfect work results at odd angles with accurate guiding of the driver blade and pin
- Precision work at full power thanks to brushless motor and optimized coil spring system
- Damage prevention thanks to dry fire lock-out that stops blank firing when the magazine is empty
- Quick and easy depth setting with precision stepless depth adjustment feature



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

