



Relays, Contactors & Switches > Switches > Rocker Switches



Rocker Switch Type: **Power**  
Rocker Switch Mounting Type: **Panel**  
Indicator/Imprint Legend: **None**  
Panel Cutout Size: **30.2 x 22.2 mm [ 1.19 x .874 in ]**  
Switch Contact Plating Material: **Silver Tin Oxide**

Features

Product Type Features

Product Type	Switch
Rocker Switch Type	Power
Lamp	Without
Rocker Switch LED	Without
Actuator Type	Top
Actuator Style	Rocker

Configuration Features

Indicator/Imprint Legend	None
Panel Cutout Size	30.2 x 22.2 mm[1.19 x .874 in]
Configuration (Pole-Throw)	Double Pole - Single Throw
Operating Function	On Off

Electrical Characteristics

Rocker Switch Voltage Rating	125 VAC, 250 VAC
------------------------------	------------------

Body Features

Beveled Frame Color	Black
Body Color	Black
Actuator Color	Black

Contact Features



Terminal Tab Width	6.35 mm[.25 in]
Switch Contact Plating Material	Silver Tin Oxide
Rocker Switch Contact Current Rating	6 A

Termination Features

Termination Type	Lead Wire - Hooking Type
------------------	--------------------------

Mechanical Attachment

Mounting Angle	Vertical
Rocker Switch Mounting Type	Panel

Housing Features

Process Sealed	No
----------------	----

Industry Standards

VDE Tested	No
------------	----

Other

Comment	Dust Resistant., Non-Illuminated
---------	----------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Hand solderable with lead free solder


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous




materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 2-6437630-0  
FTD0904=MINIATURE TOGGLE




TE Part # 5-6437630-0  
AWTR1504 = POWER TOGGLE



TE Part # 6-6437630-1  
FTN59G04=LOCKING TOGGLE




TE Part # 8-6437630-0  
A4TK15W04




TE Part # 7-6437630-2  
AWTN1504 = POWER TOGGLE


Customers Also Bought




TE Part #7-1393211-1  
T92P7D22-24




TE Part #1623403-1  
CRG1206 1% 100R




TE Part #3-1879234-7  
SMF5 16K 5%




TE Part #2-1393240-5  
RT33K048




TE Part #2-6437630-9  
FLD29BLACK04=ROCKER ACTION SWITC



TE Part #4-6437630-7  
FLN29RED04=ROCKER ACTION SWITCH



TE Part #EC0726-000  
06163942



TE Part #EC0963-000  
06173942

Documents

Product Drawings  
FLN29BLACK04=ROCKER ACTION SWITC



English

Datasheets & Catalog Pages  
[SWITCHES\\_CORE\\_PROGRAM\\_CATALOG](#)

English

[F\\_SERIES\\_SWITCHES\\_QUICK\\_REF\\_GUIDE\\_1-1773458-9](#)

English