## suction cup ESS-40-CS Part number: 189405

**FESTO** 



easily interchangeable,





## **Data sheet**

Feature	Value
Suction cup height compensator	12.8 mm
Min. workpiece radius	100 mm
Nominal size	3 mm
suction cup diameter	40 mm
suction cup volume	19.72 cm3
Position of connection	on top
Assembly position	Any
Correlation to suction-cup holder	Size 4
Suction cup shape	Round, bellows, 3.5 convolutions
Operating pressure	0 0.95 bar
Nominal operating pressure	-0.7 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	1 - Low corrosion stress
Food-safe	See Supplementary material information
Ambient temperature	-30 180 °C
Retention force at nominal operating pressure	42.4 N
Lateral force at nominal operating pressure	13 N
Product weight	21.9 g
Mounting type	Via vacuum port
Vacuum connection	M6
Colour	transparent
Shore hardness	50 +/- 5
Material of threaded plug	Wrought aluminium alloy, nickel-plated
	Nickel-plated brass
	Galvanised and chrome-plated steel
Materials note	Free of copper and PTFE
	Contains PWIS substances
	Conforms to RoHS
Material suction cup	VMQ (silicon)