

250mm High

400mm High



A



B



C

Model	Drawers (Qty x Front Height mm)	525mm Deep		650mm Deep		750mm Deep	
		Order Ref.	Price £	Order Ref.	Price £	Order Ref.	Price £
A	1x 150	40011035.11V	249.82	40019001.11V	259.35	40027092.11V	280.23
B	2x 150	40011037.11V	322.39	40019005.11V	334.97	40027108.11V	343.28
C	3x 100	40011068.11V	378.49	40019009.11V	390.12	40027096.11V	434.08

600mm High



D



E



F

Model	Drawers (Qty x Front Height mm)	525mm Deep		650mm Deep		750mm Deep	
		Order Ref.	Price £	Order Ref.	Price £	Order Ref.	Price £
D	500 door	40011060.11V	283.51	40019118.11V	286.82	40027098.11V	318.69
E	2x 75, 1x 150, 1x 200	40011040.11V	464.53	40019015.11V	482.43	40027100.11V	527.49
F	2x 75, 2x 100, 1x 150	40011061.11V	520.63	40019152.11V	540.67	40027102.11V	587.93

700mm High



G



H



I

Model	Drawers (Qty x Front Height mm)	525mm Deep		650mm Deep		750mm Deep	
		Order Ref.	Price £	Order Ref.	Price £	Order Ref.	Price £
G	1x75, 1x 100 / 400 door	40011041.11V	428.49	40019021.11V	443.97	40027001.11V	474.74
H	1x 100, 2x 150, 1x 200	40011062.11V	481.39	40019025.11V	492.32	40027005.11V	540.67
I	2x75, 1x 100, 1x 150, 1x 200	40011042.11V	537.11	40019027.11V	550.52	40027007.11V	601.03