



No. 135



E-3



PE-2



PEO-2



PEG-2

**No. 135 Series Pocket Levels with satin nickel-plated finish 2-1/2 and 3-1/2" / 63 and 88mm**

Another extremely useful Starrett level that fits handily in the pocket with no sharp edges. Made from hexagonal stock with convex ends and satin nickel-plated finish.

**No. E-3 Aluminum Line/Pocket Level 3"/7.5cm**

Lightweight, durable aluminum construction prevents line sag. Sure-grip line hooks hold line and allow level to slide freely. Flat base for accurate surface leveling. Large vial sight. Permanently marked for fast, dependable readings.

**No. PE Series Colored Line/Pocket Levels with V-grooved base 3"/7.5cm**

Lightweight, rugged plastic construction prevents line sag. Sure-grip line hooks hold line and allows level to slide freely. V-grooved base for surface leveling and tubular work. Large top and bottom vial sights. Permanently marked level vial for fast, dependable readings. Handy pocket clip. Available in red or high-visibility orange or green.

**BE-1 Bull's-Eye Circular Level**

Level with all purpose, circular vial has full 360 degree viewing. Sturdy plastic construction. Large sight for ease of reading. Ideal for home, workshop and industry. Level appliances, turntables, etc. Carry in your pocket. Size is 1-3/4" (44mm) in diameter.



BE-1

**Line/Pocket Levels**

Description		Catalog No.	EDP No.
135 Series Pocket Levels with Main Vial	2-1/2"/63mm	135A	50570
	3-1/2"/88mm	135B	50571
PE Series Line/Pocket Levels w/V-grooved base, 1-Vial Level with Line Hooks and Pocket Clip	Red	PE-2	36076
	Orange	PEO-2	36265
	Green	PEG-2	36266
E-3 Aluminum Line/Pocket Level, 1-Vial Level with Line Hooks	3"/75mm	E-3	36077

**Bull's Eye Circular Level**

1-3/4" Circular Level	BE-1	36078
-----------------------	------	-------

## A-9, M-9 Aluminum Torpedo Levels with grooved or magnetic base 9"/23cm

These levels have a cast aluminum frame with working surfaces that are lapped for accuracy. The No. A-9 has a V-grooved base for plumbing and tubular work. The No. M-9 has a strong magnet set in the base to hold the level securely to iron and steel surfaces.

## AM-9 Aluminum Torpedo Level with magnetic base and grooved top surface 9" / 23mm

Our best torpedo level ... This level has a cast aluminum frame with working surfaces that are lapped for accuracy. Features rare earth magnets that hold the level securely to iron and steel surfaces. The V-grooved top working surface is ideal for plumbing and tubular work.

## PLM Series Colored Torpedo Levels with magnetic base and grooved top edge 9"/23cm

Get a level that is easy to see on your bench. Choose from neon orange or yellow.

Levels feature a precision molded, high-impact styrene frame, a magnetic base which holds securely to ferrous surfaces, and a V-grooved top edge for plumbing or tubular work.

### Torpedo Levels

Torpedo levels are handy tools that find their way into most tool boxes. They are relatively small, are light but sturdy, and come in a variety of styles.

All of our torpedo levels have three vials; a top and side reading level, plumb, and 45° miter. Each vial is precision mounted, requiring no adjustment.

All feature hang holes as well.



### Torpedo Levels

Description		Catalog No.	EDP No.
Aluminum Torpedo Levels with grooved or magnetic base with 3 Vials (1 Plumb, 1 Level, 1 45°), Side and Top Reading	V-Grooved	A-9	36069
	Magnetic	M-9	36070
With 3 Vials (1 Plumb, 1 Level, 1 45°), Side and Top Reading		AM-9	36071
With 3 Vials (1 Plumb, 1 Level, 1 45°), Side and Top Reading	Yellow	PLMY-9	12171
	Orange	PLMO-9	64409