



Product data sheet

Power tools for trade & industry

Random Orbit Sander

PRO GET 55-125



125mm turbo sander with outstanding control

The most important data

Rated input power	550 W
Sanding pad diameter	125 mm
Orbit diameter	3.5 mm

Order number 0 601 257 070

Technical data

Additional data

Rated input power	550 W
Sanding pad diameter	125 mm
Orbit diameter	3.5 mm
Weight	2.4 kg
No-load speed	3,300 – 7,800 rpm
Orbital stroke rate	6,600 – 15,600 opm
Sanding pad speed	200 – 480 rpm
Eccentricity	1.75 mm
Sanding sheet / disc attachment	hook-and-loop fastening

Noise/vibration information

Sanding solid wood

Vibration emission value ah	6 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Perfectly designed ergonomic palm rest and handle with gripping circumference of only 18 cm provide best tool control
- Multi-hole sanding pad for sanding sheets with different hole pattern and for significantly increased dust extraction
- Extremely powerful 550 Watt motor and direct driven pad rotation deliver up to 27% higher removal rate

**HEAVY
DUTY**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/lb/en/wac/>

