



Part Number : [1300950196](#)

Product Description : Junior Duty Wire Mesh Pulling Grip, Single Weave, Flexible Eye, Mesh Length 0.178m (7.00"), Approximate Break Strength 771.11kg (1700 lbs)

Series Number : 130095

Status : Active

Product Category : Cable Grips

Engineering Number : 35971



Documents & Resources

Drawings

[1300950196_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Cable Grips
Series	130095
Description	Junior Duty Wire Mesh Pulling Grip, Single Weave, Flexible Eye, Mesh Length 0.178m (7.00"), Approximate Break Strength 771.11kg (1700 lbs)
Product Name	Junior Duty
Type	Pulling Grip
UPC	78678835971

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	771.11kg (1700 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	9.40-12.45mm (.370-.490")
Color - Grommet	N/A
Eye Type	Flexible
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.178m (7.00")
Net Weight	20.865/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

This document was generated on Mar 27, 2025