



6-569542-3 | MP-88S-F-1  
**Modular Plug, 8P/8C, Shielded, Flat Oval, 100 pcs**

## Body Features

Conductor Type	Solid   Stranded
Shield Material	Copper alloy
Shield Plating Material	Nickel

## Configuration Features

Number of Positions	8
Keyed	No

## Contact Features

Contact Base Material	Phosphor bronze
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 $\mu\text{in}$   1.27 $\mu\text{m}$
Number of Contacts Loaded	8

## Dimensions

Cable Jacket Outside Diameter Range	2.54–8.89 mm   0.10–0.35 in
Conductor Outside Diameter	0.034–0.039 in   0.86–0.99 mm
Conductor Wire Size	26–24 AWG

## Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

## Industry Standards

UL Flammability Rating	UL 1863
------------------------	---------

## Packaging Features

Packaging Quantity	100
--------------------	-----

## Product Availability

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

## Product Type Features

Cable Type	Flat oval, shielded
Performance Category	Category 5

6-569542-3 | MP-88SF-1

Connector Style	Plug
Jack Type	RJ45
Latch Style	Standard
Product Type	Connector
Shielded	Yes

## Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
----------------------------------	-------------------------------------