coupling socket NPHS-D6-P-BC9 Part number: 8059274



Data sheet

Feature	Value
Nominal size	7 mm
Operating pressure complete temperature range	-0.95 10 bar
Standard nominal flow rate	1,448 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 60 °C
Product weight	95 g
Pneumatic connection, port 1	for barbed connector internal diameter 9 mm
Materials note	Conforms to RoHS

FESTO