

M18 BLIDRC-402C

M18™ COMPACT BRUSHLESS 1/4" HEX IMPACT DRIVER

- Brushless impact driver measures only 112 mm in length making it ideal for working within confined spaces
- Brushless motor technology delivers 190 Nm of torque, 3600 rpm and 4900 ipm
- One-handed bit insert with retention lock, for faster, easier changing of bits
- Heavy duty full metal gearbox and gears for superior durability and maximum torque
- On board fuel gauge and LED light
- All metal reversible belt clip to hang your tool quickly and easily
- Brushless motor, REDLITHIUM™ battery pack and REDLINK™ electronic deliver power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



No load speed (rpm)	0 - 3600
Impact rate (ipm)	0 - 4900
Tool reception	1/4" Hex
Max. torque (Nm)	190
Weight with battery pack (EPTA) (kg)	1.3 (M18 B4)
Kit included	2 x M18 B4 Battery packs, M12-18 C Charger, Kitbox
Article Number	4933492840