

Sales Presenter

Store n Go V3 USB Drive – USB 3.0 Super Speed

Overview

Verbatim's new USB 3.0 Flash Drive; the Store n Go V3 Drive will be launched in a range of capacities from 8GB up to 64GB, and in colour variants as follows:

| | |
|--------------------|----------------------------|
| Grey: | 8GB, 16GB, 32GB, and 64GB. |
| Sun kissed Yellow: | 16GB |
| Caribbean Blue: | 16GB |
| Eucalyptus Green: | 16GB |
| Hot Pink: | 16GB |
| Volcanic Orange: | 16GB |
| Violet: | 16GB |

V3 offers a USB 3.0 interface which is up to 10 times faster than USB 2.0 (Theoretical Bus Speed), making it faster for transferring/saving larger file sizes of all types.

Available: April



Sales Presenter

Store n Go V3 USB Drive – USB 3.0 Super Speed

Key Features

- USB 3.0 USB Super Speed interface
- 'Slide and Lock' mechanism. Locks into position when using the drive, and retracts back into a closed position to protect the interface when not in use.
- Small form factor with a tapered design
- 64GB capacity to store larger media files (Video / Photo)
- 2 Year Limited Warranty

Available: April



Sales Presenter

Specifications

- Drive capacity: 8GB, 16GB, 32GB, 64GB
- Read Speed: 8GB up to 40MB/sec
16GB up to 60MB/sec
32GB up to 80MB/sec
64GB TBC
- Write Speed: 8GB up to 12MB/sec
16GB up to 12MB/sec
32GB up to 25MB/sec
64GB TBC
- Drive Type: USB Flash Drive
- Interface: USB 3.0 – backwards compatible with USB 2.0
- Format: FAT 32
- Packaging: Paper board retail packaging
- Pack contents: V3 Store n Go Drive



Sales Presenter

Part number & Bar Codes

| P/N/Capacity/Colour | Bar code | EAN128 code | EAN14 code |
|-----------------------------|-----------------|----------------------------------|------------------|
| 49171 8GB Grey | 0 23942 49171 2 | (02) 00 023942 49171 2 3710 9158 | 50023942 49171 7 |
| 49172 16GB Grey | 0 23942 49172 9 | (02) 00 023942 49172 9 3710 9158 | 50023942 49172 4 |
| 49173 32GB Grey | 0 23942 49173 6 | (02) 00 023942 49173 6 3710 9158 | 50023942 49173 1 |
| 49174 64GB Grey | 0 23942 49174 3 | (02) 00 023942 49174 3 3710 9158 | 50023942 49174 8 |
| 49175 16GB Sunkissed Yellow | 0 23942 49175 0 | (02) 00 023942 49175 0 3710 9158 | 50023942 49175 5 |
| 49176 16GB Caribbean Blue | 0 23942 49176 7 | (02) 00 023942 49176 7 3710 9158 | 50023942 49176 2 |
| 49177 16GB Eucalyptus Green | 0 23942 49177 4 | (02) 00 023942 49177 4 3710 9158 | 50023942 49177 9 |
| 49178 16GB Hot Pink | 0 23942 49178 1 | (02) 00 023942 49178 1 3710 9158 | 50023942 49178 6 |
| 49179 16GB Volcanic Orange | 0 23942 49179 8 | (02) 00 023942 49179 8 3710 9158 | 50023942 49179 3 |
| 49180 16GB Violet | 0 23942 49180 4 | (02) 00 023942 49180 4 3710 9158 | 50023942 49180 9 |

Sales Presenter

Packaging Configuration

| | |
|---------------------|---|
| Product Dimensions: | 58mm x 20mm x 11mm (L x W x H) |
| Product weight: | 10 grams |
| Pack dimensions: | 90mm x 12.5mm x 135mm (W x D x H) |
| Pack weight: | 20 grams |
| Units per carton: | 10 |
| Carton dimensions: | 95.25mm x 139.7mm x 73.02mm (W x H x D) |
| Cartons per pallet: | 840 |
| Layers per pallet: | 7 |
| Units per pallet: | 8400 |

Languages:

Front of pack: English / French

Back of pack:

ENG, FRE, GER, IT, SP, POR, POL, RUS, CZ, H, SER, CRO, Simplified Chinese, and Korean

System requirements:

Windows 7, Vista, XP

Mac OS X 10.4 or higher

Linux 2.4.0 or higher