



Years Warranty*

ANSMANN Pure Power Li-Ion battery AAA / HR03 type 1400 (min. 1250 mAh)

AAA / HR03 Lithium-ion batteries – 1,5 V / type 1400 (min. 1250 mAh) / 1,93 Wh – Batteries with maximum capacity, long runtime and protection technology, ideal for devices with high energy requirements

Features

- High-quality Pure Power AAA / HR03 lithium batteries
- Pure performance: high capacity, power and runtime – even in cold conditions
- Ideal for use in modern LED torches, headlamps, toys, wildlife cameras, etc.
- Integrated protective circuitry protects against overcharging, overload, short circuit and deep discharge
- Max. Continuous discharge current: 1,5 A
- Very low self-discharge and high energy efficiency
- Excellent price-performance ratio
- 2 years guarantee



Up to 2000 charging cycles



Safety board inside



Low Self Discharge



Article number: 1311-0034

Product content: Lithium rechargeable battery type AAA /
HR03 / 1400 mAh



Specifications

Nominal voltage	1,5 V
Cell size	AAA / HR03
Cell chemistry	Lithium ion
Nominal capacity	1400 mAh
Minimum capacity	1250 mAh
Number of cells in packaging	4
Fast charging	Yes
Charging cycles	1500
Max. Continuous discharge current	1,5 A
Energy	1,93 Wh
suitable for	LED torches, headlamps, toys, wildlife cameras, etc.
Color	pink / yellow
Packaging	cardboard box
Operating temperature	-20 - 60 °C
Storage temperature	-20 - 25 °C
Dimensions	× × mm