

## Plug-in card block - SKBI 32/D - 2261054

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug-in card block, Nominal current: 4 A, Number of positions: 32, Pitch: 5.08 mm, Connection method: Screw connection, Color: green



### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 053826
Weight per Piece (excluding packing)	154.0 g
Custom tariff number	85369010
Country of origin	Germany

### Technical data

#### Dimensions

Length	43 mm
Height	138 mm
Width	112 mm
Pitch	5.08 mm
Hole diameter	4.2 mm

#### General

Range of articles	SKBI 32
Connection in acc. with standard	EN-VDE
Nominal current $I_N$	4 A
Nominal voltage $U_N$	250 V
Nominal cross section	2.5 mm <sup>2</sup>
Stripping length	8 mm
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm
Number of positions	32

# Plug-in card block - SKBI 32/D - 2261054

## Technical data

### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260710
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002642
ETIM 5.0	EC002780

### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals

### Approvals

---

### Approvals

### GOST / GOST

---

### Ex Approvals

---

# Plug-in card block - SKBI 32/D - 2261054

## Approvals

Approvals submitted

### Approval details



## Accessories


### Accessories

Foot element - SF-SKBI 31/32 - 2261009

Snap foot, for horizontal or vertical mounting of the SKBI plug-in card blocks, on the NS 35/7.5 DIN rail

## Drawings

Dimensioned drawing



Schematic diagram

