



22MM PLASTIC ROUND COMPLETE UNIT
 COMBINATION: INDICATOR LIGHT WITH SMOOTH
 LENSE NON-ILLUMINATED WITH LAMP HOLDER BA 9S
 WITHOUT LAMP SPRING-LOADED TERMINAL WITH
 HOLDER YELLOW

Actuator / signaling device:

Design of the operating mechanism		indicator light
Color / of the activation element		Yellow
Material / of the activation element		plastic
Shape / of the activation element		Smooth lens
Number of switching positions		0
Product component / front ring		No
Product function / EMERGENCY STOP function		No

Contact block / lampholder

Design of the electrical connection		spring-loaded terminals
Number of switching elements		0
Number of NC contacts / for auxiliary contacts		0
Number of NO contacts / for auxiliary contacts		0
Number of change-over switches / for auxiliary contacts		0
Product function / positive opening		No
Number of lampholders		1
Execution of the mounting		BA 9s, without lamp
Product component / fluorescent materials		No
Product extension / optional / fluorescent materials		Yes

Accessories:**Product component / holder for 3 switching elements**

No

General technical details:**Type of voltage / of the operating voltage**

AC/DC

Operating voltage / rated value

• minimum

V

5

• maximum

V

400

Resistance against shock

• for devices with incandescent lamp / according to IEC 60068-2-27

<= 30g

• for devices without incandescent lamp / according to IEC 60068-2-27

<= 50g

Resistance against vibration / according to IEC 60068-2-6

20 ... 200 Hz: 5g

Item designation

• according to DIN EN 61346-2

P

• according to DIN 40719 extendable after IEC 204-2 / according to IEC 750

H

Tightening torque / of the screws in the bracket / maximum

N·m

1

Ambient temperature

• during operating

°C

-25 ... +60

• during storage

°C

-40 ... +80

Protection class IP

IP66

climatic class / during the operating phase / according to EN 60721

3K6

Type of mounting

front mounting

Shape / of the installation hole

round

Installation width

mm

28

Mounting diameter

mm

22

Mounting height

mm

11

Mounting depth

mm

49

Certificates/approvals:

General Product Approval	Declaration of Conformity	Test Certificates
--------------------------	---------------------------	-------------------



CCC



CSA



GOST



UL



EG-Konf.

[Special Test Certificate](#)

Shipping Approval



ABS



BUREAU
VERITAS



DNV



LRS



PRS



RINA

other

[Confirmation](#)

[other](#)

[Environmental Confirmations](#)

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

Cax online generator:

<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB3204-6AA30-0CC0/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3204-6AA30-0CC0

last change:

Jul 17, 2012