

Features

- Multi-language support
- Free Type and Windows Font support
- Defining user image library
- Simulation feature
- C/C++ real-time programming
- 260K Display Colour
- 800x480 Display resolution

RS PRO 5" HMI Panel

RS Stock No.: 0315660



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

BACNET MSTP,
MODBUS-RTU / -ASCII (Master / Slave) communication,
Compatible with OMRON Host Link, DELTA DVP Series PLCs.

General Specifications

| | |
|-------------------|---------------------|
| CPU | ARM Cortex-A Series |
| Flash Memory | 8GB eMMC |
| RAM | 512 MB DDR3 SDRAM |
| Backlight Life | 50000 hours |
| Luminance (Cd/m2) | 330 |

Mechanical Specifications

| | |
|-------------------|----------------|
| Device Dimensions | 153x105x40.5mm |
| Panel Cut-Out | 139x94mm |
| Weight | 350gr |

Electrical Specifications

| | |
|--------------------|--|
| Operation Voltage | 18...30Vdc |
| Power Consumption | 5W (5") |
| RTD Battery / Life | CR2023 Button Cell Lithium bat. / 3V - 5 years |

Protection Category

| | |
|------------------|------|
| Protection Class | IP65 |
|------------------|------|

Approvals

| | |
|---------------------------|----------------|
| Compliance/Certifications | CE Certificate |
|---------------------------|----------------|

Electrical Connection

