

Product Datasheet XVR107S

witty one charging station 1x07kW 1ph+N Type 2S socket

Power

Maximum power per charging point: 7 kW

Connected power: 0.1 - 7 kW

Frequency

50 - 60 Hz

Power supply

Number of phases: 1

Electric current

Rated current: 32 A

Connectivity

Number of charging points: 1

Functions

Load management: No

Equipment

Domestic sockets: 0

Protection circuit breaker: No

Emergency trip in case of power outage: Yes

Connection

Connector/socket type: Type 2S

Dimensions

370 x 250 mm

Height: 370 mm

Width: 250 mm

Depth: 150 mm

Installation

Wall mounted

Safety

Protection rating: IP55

Impact resistance: IK10

Operating conditions

Operating temperature: -25 to 50 °C

Voltage

Rated voltage: 400 - 400 V

Material

Plastic

Sustainability

RoHS compliant: Yes

Photos | Drawings

Original product photos/drawings were present in the source datasheet. This English version reproduces the translated content.