



Flashlight element, with integrated LED, clear, 115 V AC, Diameter 70 mm

product brand name	SIRIUS		
product designation	Repeated-flash light element		
design of the product	including light sources		
General technical data			
type of voltage of the operating voltage	AC		
operating voltage			
• 1 at AC at 50 Hz rated value			
• 1 at AC at 60 Hz rated value	115 V		
relative positive tolerance of the operating voltage	10 %		
relative negative tolerance of the operating voltage	-10 %		
consumed current maximum	25 mA		
reference code according to EN 61346-2	P		
Lamp			
product component light source	Yes		
type of light source	LED		
service life of LED	100 000 h		
design of the optical signal	blinklight		
light intensity	1.04 cd		
light intensity	0.73 ... 1.52 cd		
flashing frequency	1 Hz		
Enclosure			
height	65.5 mm		
width	70 mm		
outer diameter of the signal column element	70 mm		
material	PC		
color	clear		
fastening method	Bayonet		
protection class IP	IP65		
Ambient conditions			
ambient temperature during operation	-20 ... +50 °C		
Approvals Certificates			
General Product Approval		other	Environment



[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD4440-5BE>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD4440-5BE>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/8WD4440-5BE>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD4440-5BE&lang=en



-P



last modified:

4/1/2025 