



verso pedestal bench with 2 drawer-door cabinet. Featuring a robust, steel channel pedestal leg, bott verso cabinet and a 30mm lino worktop. Cabinet size - WxDxH: 525x550x900mm. Drawer configuration: 1x 125mm, 1x 175mm with 100% extension slides (75kg U.D.L.) and a single, reinforced door and 1 adjustable height, galvanised steel shelf (75kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 7016 anthracite grey. WxDxH: 1500x600x930mm.

Breite [mm]: 1500  
Tiefe [mm]: 600  
Höhe [mm]: 930  
Bruttogewicht [kg]: 75.08  
EAN-Code: 5039350096802  
Zolltarifnummer UK: 94032080  
Ursprungsland: GB

## Produkteigenschaften

|                      |                 |
|----------------------|-----------------|
| Product surface      | Powder coated   |
| Product material     | Sheet steel     |
| Main colour          | Anthracite grey |
| Main RAL colour      | RAL 7016        |
| Secondary colour     | Light grey      |
| Secondary RAL colour | RAL 7035        |

## Artikelbeschreibungen

|               |       |
|---------------|-------|
| Product brand | verso |
|---------------|-------|

## Schubladen

|                           |     |
|---------------------------|-----|
| Number of drawers         | 2   |
| Drawer load capacity [kg] | 75  |
| Drawer height 1 [mm]      | 125 |
| Drawer height 2 [mm]      | 175 |

## Schrank, Gehäuse, Werkbank und EAP

|                          |       |
|--------------------------|-------|
| Worktop/housing top type | Lino  |
| Shelf load capacity [kg] | 75    |
| Door type                | Plain |
| Door height 1 [mm]       | 500   |