



www.cif.fr

**Coper clad
1 side FR4
AD16**

This document contains manufacturer's information, protected through copyright. All rights reserved. This document can not be copied, reproduced or translated without written agreement from **C.I.F**

Information contained in this document can be modified without any prior notice

Characteristics

Epoxy base 16/10th - 35 μ

Size in mm: 100 x 160

- High qualified stratified
- 8 glass tissue layers
- Standard MIL 13949 F for FR4
- UL 94 VO
- tolerance of +/- 1%: dim. max 101,0x161,6mm / dim. mini 99,0x158.4mm

For other characteristics, see special datasheet for FR4

Storage

Keep boards in dry and fresh room.

cif@cif.fr