Part Number : 1301530089
Product Description : Safeway User Attachable GFCI Right-Angle Plug, Manual Reset, NEMA 5-15, 15A, 120V
Series Number : 130153
Status : Active
Product Category : Power Distribution
Engineering Number : 15054



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active

Category	Power Distribution
Series	130153
Description	Safeway User Attachable GFCI Right-Angle Plug, Manual Reset, NEMA 5-15, 15A, 120V
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-15
Product Name	Safeway
Type	GFCI Commercial Duty, Single Phase
UPC	78678828425

Agency

CSA	LR6837
UL	E66308

Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes - Plug
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	120V AC

Physical

Cord Diameter	N/A
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	N/A
Cord Type	N/A
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Mounting Style	Portable
Net Weight	162.386/g
Number of Receptacles	0
Packaging Type	Carton

Receptacle Type	N/A

This document was generated on Mar 27, 2025