




Product Datasheet

High Pressure Fitting

((

ASME B16.11

Threaded 90 Elbow





3000 LB												
RS Code	Size		A		Н		G (Min)		Length Of Thread (Min)			
									В		L2	
	DN	NPS	mm	in	mm	in	mm	in	mm	in	mm	in
826-6914	8	1/4"	25	0.98	25	0.98	3.3	0.13	8.1	0.32	10.2	0.4
826-6918	10	3/8"	28	1.1	33	1.3	3.51	0.14	9.1	0.36	10.4	0.41
826-6927	15	1/2"	33	1.3	38	1.5	4.09	0.16	10.9	0.43	13.6	0.54
826-6920	20	3/4"	38	1.5	46	1.81	4.32	0.17	12.7	0.5	13.9	0.55
826-6924	25	1"	44	1.73	56	2.2	4.98	0.2	14.7	0.58	17.3	0.68
826-6933	32	1-1/4"	51	2.01	62	2.44	5.28	0.21	17	0.67	18	0.71
826-6936	40	1-1/2"	60	2.36	75	2.95	5.56	0.22	17.8	0.7	18.4	0.72
826-6930	50	2"	64	2.52	84	3.31	7.14	0.28	19	0.75	19.2	0.76

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.