



Datasheet

Stock No: 811-4407

ENGLISH

RS Pro BASEC 5 Core White Unscreened 3185Y Stranded PVC Power Cable H05VV-F, 1.5 mm² CSA 15 A 100m, 300/500 V



Product Details

BASEC approved H05VV-F/3185Y 5 Core Cable

Flexible PVC Cable

Specifications:

Number of Cores	5
Cross Sectional Area	1.5 mm ²
Sheath Colour	White
Current Rating	15 A
Voltage Rating	300/500 V
Reel Length	100m
Outer Diameter	3mm
Sheath Material	Polyvinyl Chloride PVC
Harmonised Code	H05VV-F
Type	3185Y
Minimum Operating Temperature	-15°C
Screened/Unscreened	Unscreened
Conductor Strand Type	Stranded
Insulation Material	PVC Type TI1 to BS7655
Length	100m
Conductor Material	Copper
Size of Strands	0.25 mm
Standards Met	BASEC
Conductor Resistance	13.3 Ω/km
American Wire Gauge	15 AWG
Core Strands	30/0.25 mm
Number of Strands	30