



Example image

APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For service water and process water
- For compressed air (oil purity class 0–3)

- For negative pressure
- For inert gases (e.g. nitrogen)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed up to ø ≤ 54 mm

- Seal ring made of CIIR, black, up to ø ≤ 54 mm
- Seal ring made of EPDM, black, from ø > 54 mm
- Pressing socket with transparent protection plug

TECHNICAL DATA

Product material	Cu-DHP copper CW024A (EN 1412)
------------------	--------------------------------

Art. no.	DN	d, ø mm	E cm	L cm	Z cm
62102	12	15	2.5	8	3
62103	15	18	2.5	8	3
62104	20	22	2.5	8.4	3.4
62105	25	28	3	9.1	3.1
62106	32	35	3	10.2	4.2

Art. no.	DN	d _ø mm	E cm	L cm	Z cm
62107	40	42	4	12	4
62108	50	54	4	14	6
62110	65	66.7	5	22	12
62111	65	76.1	5.3	23	12.4
62112	80	88.9	6	26	14
62113	100	108	7.5	31	16