



Product data sheet

Power tools for trade & industry

EXACT ION 8-1100 WK

INDUSTRIAL EXACT ION 8-1100 WK



The new EXACT screwdrivers – now with lithium-ion technology!

The most important data

Torque (hard)	2 – 11 Nm
Speed	78 – 780 rpm

Part Number 0 602 494 407

Technical data

Technical data

Description	Centre grip screwdriver with angle flange
Torque, from (hard)	2 Nm
Torque, to (hard)	11 Nm
Torque (hard)	2 – 11 Nm
Torque, from (soft)	2 Nm
Torque, to (soft)	11 Nm
Torque (soft)	2 – 11 Nm
Speed, from	78 rpm
Speed, up to	780 rpm
Speed	78 – 780 rpm
Direction of rotation	R/L
Weight	1.4 kg
Comment	Values measured with 2.0 Ah battery and angle head 0 607 453 620 Below 50% speed setting eventually lower power
Bit holder	Without angle head
Battery	18 V / 2.0 Ah battery
Drive type	Battery
Design	Centre grip

Connector type	Shut-off clutch
----------------	-----------------

Noise/vibration information

Screwdriving

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

