

56732

Hand shovel, 327 x 271 x 50
mm, 550 mm, Green



Lightweight and durable hand shovel. Its one piece construction eliminates areas where bacteria can be harboured. Smooth surface makes it extremely easy to clean, ideal for use in food production areas for moving food ingredients or large quantities of food waste.

Technical Data

Item Number	56732
Shovel Blade Size, L x W x H	327 x 271 x 50 mm
Material	Polypropylene
Suitable for Food Contact (EU 1935/2004), ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	12 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	240 Pcs.
Quantity Per Layer (Pallet)	48 Pcs.
Box Length	600 mm
Box Width	335 mm
Box Height	320 mm
Length	550 mm
Width	275 mm
Height	110 mm
Gross Weight	0,545 kg
Net Weight	0,509 kg
Cubik metre	0,0166 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Max. drying temperature	120 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Recycling Mark 7	Yes
GTIN-13 Number	5705020567322
GTIN-14 Number (Box quantity)	15705020567329
Commodity Code	39241000
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

1. See Declaration of Compliance for further details on food contact