



tesa® 64286

Product Information



Strapping tape for basic applications

Product Description

tesa® 64286 is a tensilized polypropylene strapping tape with a hot melt adhesive system.

tesa® 64286 exhibits a good tensile strength with low elongation at the same time. The product shows a high peel adhesion.

Product Features

- good tensile strength with low elongation at the same time
- high peel adhesion

Application Fields

- Palettizing
- Reinforcing
- Closing of shipping cartons

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|------------------|-------------------|-------|
| • Backing | MOPP | • Total thickness | 73 µm |
| • Type of adhesive | synthetic rubber | | |

Properties/Performance Values

- | | | | |
|-----------------------|------|--------------------|----------|
| • Elongation at break | 35 % | • Tensile strength | 175 N/cm |
|-----------------------|------|--------------------|----------|

Adhesion to Values

- | | |
|---------|----------|
| • Steel | 7.5 N/cm |
|---------|----------|



tesa® 64286

Product Information

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=64286>