

COLD WATER HIGH-PRESSURE CLEANER

TradePro HD 200

Professional quality and performance in a truly portable package with convenient shoulder strap and carry handle. Thanks to its compact dimensions and light weight, it's easy to transport even up steps or ladders. High-end features include automatic pressure relief to protect internal components on start-up, Easy Press trigger gun with rotating lance, and high-grade hose and power cable. All of its professional-grade accessories are stored on-board, providing easy access and helping to prevent trip hazards. This tough, simple machine can be operated in a vertical or horizontal position, making it safer for use at height or on uneven ground.



Technical Specification

Cold Water High-Pressure Cleaner	HD 200
Operating pressure (bar):	130
Flow rate (l/h):	400
Performance (kW):	2.1
Weight (kg):	20.5



Practical accessory storage

- Clever design with practical on-board accessory, hose and cable storage
- Helps protect against trip hazards and loss



Robust stability

- Flexible stability; operate upright or lie flat



German Engineering

- Longevity and reliability; hardwearing components include high-quality brass cylinder head and 3-piston axial pump



Mobility

- Lightweight product delivers first-class mobility
- The HD 200's shoulder carry strap makes transporting and loading easy