

HyFlex™

70-114

Superior mechanical protection and cut-resistance

Previously known as: Neptune® Kevlar®



Cut



Medium Duty

Kevlar®-lined arm protection sleeves, offering cut resistance and heat protection

- **Elevated comfort:** HyFlex® 70-114 arm protection sleeves feature high-tech 100% Kevlar® para-aramid short fibers and an automatic knit liner, providing wearers with outstanding comfort
- **Advanced defenses:** Their blend of Kevlar® para-aramid short fibers also imparts excellent cut resistance capabilities, while ensuring contact heat protection up to 100°C/212°F
- **Enhanced features:** In addition, these protective sleeves feature a practical thumb slot, for a secure fit and extra wrist protection



Industries

- Automotive
- Metal fabrication
- Machinery and Equipment

Applications

- Press shop operations
- Assembly & inspection of components
- Applying sealers, touching up
- Equipment repair & maintenance
- Cutting glasses, sheets, panels
- Seizing structural and body parts
- Adjusting systems and screwing

HyFlex™

70-114

Superior mechanical protection and cut-resistance

Previously known as: Neptune® Kevlar®

Key Features

- **Kevlar® para-aramid short fibers:** Superb comfort and cut resistance
- **Heat-resistant design:** For contact heat protection up to 100°C/212°F
- **Thumbslot:** Secure fit and additional wrist protection

Performance Standards & Regulatory Compliance



Technologies

Kevlar®

Specifications

BRAND STYLE	DESCRIPTION	Gauge	LENGTH	PACKAGE
HyFlex® 70-114	Liner Material: Kevlar® Cuff Style: Knitwrist	10	14" (356 mm)	12 pieces/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.