

40108

# Stainless Steel Scraper with Threaded Handle, 50 mm, Purple



Great for removing hard-to-reach sticky deposits and dried or burnt-on foods or ingredients, this Scraper features a stainless flex steel blade with protective rounded corners, a high-strength attachment, and a threaded handle that fits any Vikan colour-coded extension handle. While not intended for floor cleaning proper, this product can be used to remove lighter soils on floors.

# Technical Data

<b>Item Number</b>	40108
<b>Material</b>	Polypropylene Stainless Steel
<b>Suitable for Food Contact (EU 1935/2004), <sup>1</sup></b>	Yes
<b>Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice</b>	Yes
<b>FDA compliant raw material (CFR 21)</b>	Yes
<b>Meets the REACH Regulation (EC) No. 1907/2006</b>	Yes
<b>Use of Phthalates (e.g. Bisphenol A)</b>	No
<b>Is Halal compliant</b>	Yes
<b>Box Quantity</b>	10 Pcs.
<b>Quantity per Pallet (80 x 120 x 200 cm)</b>	3150 Pcs.
<b>Quantity Per Layer (Pallet)</b>	150 Pcs.
<b>Box Length</b>	255 mm
<b>Box Width</b>	225 mm
<b>Box Height</b>	85 mm
<b>Length</b>	205 mm
<b>Width</b>	50 mm
<b>Height</b>	32 mm
<b>Gross Weight</b>	0,09 kg
<b>Net Weight</b>	0,08 kg
<b>Cubik metre</b>	0,0003 M3
<b>Max. usage temperature (for food contact)</b>	200 °C
<b>Max usage temperature (non food contact)</b>	200 °C
<b>Min. usage temperature</b>	-20 °C
<b>Min. pH-value in usage concentration</b>	2 pH
<b>Max. pH-value in Usage Concentration</b>	10,5 pH
<b>GTIN-13 Number</b>	5705020401084
<b>GTIN-14 Number (Box quantity)</b>	15705020401081
<b>Commodity Code</b>	82159910
<b>Country of origin</b>	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact