

Professionally approved products.

Extension Springs

Steel Extension Spring



[RS Stock No. 121-321](#)

Features:

Ends : Looped

Material : Steel

Specification:

RS Stock No.	Free Length	Outside Diameter	Spring Rate	Maximum Extended Length
121321	87.2 mm	12 mm	2.52N/mm	134.80 mm
121343	88.6 mm	24 mm	0.92N/mm	206.6 mm
121365	85.5 mm	18 mm	4.27N/mm	133.10 mm
121416	109 mm	25 mm	49.7N/mm	128 mm
751663	27.2 mm	4 mm	0.06N/mm	95.7 mm
751821	32.6 mm	9 mm	0.3N/mm	86.1 mm
751837	44.6 mm	9 mm	0.19N/mm	130.20 mm
751843	60.6 mm	9 mm	0.13N/mm	188.6 mm
751887	60.6 mm	11 mm	0.17N/mm	224.40 mm
751893	34.4 mm	12 mm	0.72N/mm	76.70 mm
751916	59 mm	8.5 mm	1.35N/mm	98.6 mm
751922	66.2 mm	13 mm	0.32N/mm	178.20 mm
751938	105 mm	15 mm	0.26N/mm	292 mm
751944	39.7 mm	11 mm	5.02N/mm	58.4 mm

