



## Single open-end spanner, 894M

**DIN 894/ISO 3318**






**Finish:** gunmetal finish.

**Material:** SPECIAL STEEL, forged.

Angle 15°.

Profiled body, with hole in the end from size 75mm to 120 mm



				<b>L</b> mm	<b>A</b> mm	<b>B</b> mm 
894M-7	1833008	10	7	78	3.2	16 10
894M-8	1833015	10	8	94	3.5	18 14
894M-9	1833022	10	9	100	4.0	20 16
894M-10	1833039	10	10	106	4.5	22 20
894M-11	1833046	10	11	112	5.0	24 23
894M-12	1833053	10	12	125	5.0	26 30
894M-13	1833060	10	13	125	5.0	29 40
894M-14	1833077	10	14	140	5.5	30 40
894M-15	1833084	10	15	140	5.5	32 49
894M-17	1833091	10	17	158	6.0	36 55
894M-19	1833107	10	19	171	7.0	40 75
894M-22	1833114	5	22	195	8.0	46 100
894M-24	1833121	5	24	216	9.0	50 150
894M-27	1833138	5	27	240	10.0	56 215
894M-30	1833145	5	30	262	11.0	62 270
894M-32	1833152	5	32	274	12.0	67 320
894M-36	1833169	5	36	303	13.0	74 400
894M-38	1833176	1	38	305	13.0	78 420
894M-41	1833183	1	41	343	14.0	85 590

894M-46	1833190	1	46	378	15.0	94 750
894M-50	1833206	1	50	413	16.0	102 945
894M-55	1833213	1	55	457	17.0	113 1185
894M-60	1833220	1	60	492	18.0	122 1380
894M-65	1833237	1	65	528	19.0	132 1750
894M-70	1833244	1	70	573	20.0	142 2270
894M-75	1833251	1	75	608	21.0	152 2770
894M-80	1833268	1	80	644	22.0	162 3180
894M-85	1833275	1	85	690	23.0	174 3630
894M-90	1833282	1	90	690	25.0	174 3630
894M-95	1833299	1	95	850	25.0	195 5750
894M-100	1833305	1	100	1000	28.0	195 5530
894M-105	1833312	1	105	1000	28.0	215 7300
894M-110	1833329	1	110	1000	28.0	215 7300
894M-115	1833336	1	115	1000	28.0	215 7300
894M-120	1833343	1	120	1000	28.0	215 7300
894M-125	0132478	1	125	1000	28	225 7300
894M-130	0132485	1	130	1000	28	225 7600
894M-135	0132492	1	135	1000	28	225 7400