

Han 16B Easy Hood side entry black



Image is for illustration purposes only. Please refer to product description.

Part number	11 30 716 0520
Specification	Han 16B Easy Hood side entry black
HARTING eCatalogue	https://harting.com/11307160520

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® Easy Hood
Type of hood/housing	Hood
Description of hood/housing	Black

Version

Size	16 B
Version	Side entry
Number of cable entries	1
Cable entry	1x Integrated
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP54
Type rating acc. to UL 50 / UL 50E	4
	4X
	12
Cable diameter	20 ... 34 mm

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated



Pushing Performance
 Since 1945

Material properties

Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	480 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140110854
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466