

Features

- Maximum operating pressure is 12 bar.
- Operating temperature range -20°C to +100°C.
- Material: Brass / Aluminum /Steel Nickel & Zinc Plated Finish
- Single Shut Off (One side is with valve)
- DN8
- ISO 4414
- ISO 6150-B-15
- Industrial Interchangeable 3/8"
- 2-Stage Safety Coupling
- Compatible with:
HANSEN 4000
PARKER 30 3/8"
CEJN 430
GROMELLE 900
RECTUS 30

RS PRO Pneumatic Quick Connect Coupling

RS Stock No.: 0325625



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Series 30S Quick Connect Couplings

Pneumatic quick-connect coupling connectors are found across industry in pneumatic systems as diverse as robotic assembly lines and other equipment.


2-Stage Security: Security is provided by pressing the button two times or by left-right sleeve twist. First press/twist releases the pressure inside the coupling and the second press/twist ejects the plug for disconnection.

- Maximum operating pressure is 12 bar.
- Operating temperature range -20°C to +100°C.
- Material: Brass / Aluminium /Steel Nickel & Zinc Plated Finish
- Single Shut Off (One side is with valve)
- DN8
- ISO 4414
- ISO 6150-B-15
- Industrial Interchangeable 3/8"
- 2-Stage Security
- Compatible with: HANSEN 4000 | PARKER 30 3/8" | CEJN 430 | GROMELLE 900 | RECTUS 30

Specifications


Manufacturer Series	030S
Coupling Type	Quick Connect Coupling Socket
Connection Standard	DN 8, ISO 4414, ISO 6150-B-15, Industrial Interchangeable 3/8"
Connection Standard Compatible With	HANSEN 4000; PARKER 30 3/8"; CEJN 430; GROMELLE 900; RECTUS 30
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+100°C
Maximum Operating Pressure	12bar
Flow	2-Stage, ISO 4414
Flow Direction & Sealing	Self-sealing coupling
Material	Brass, Aluminium
Finish	Nickel Plated
Connection Type	Threaded
Thread Size	1/4 in
Thread Standard	G
Thread Gender	Female
Coupling Gender	Female
Threaded Connection	G 1/4 in Female
Seal material	Nitrile Rubber
Hose Barb Connection	N/A

Specifications



Dimensions (mm)		
SW	L	ØD
25	77.7	29

Materials



Material Code

A = Brass Nickel Plated
 B = Zinc Plated
 C = Aluminium
 S = Steel Nickel Plated

Series 30S Quick Connect Couplings

	0 - 12 bar (0-174 PSI)		-20° to +100°C (NBR) -4° to +212°F	Shut Off Type	
	OM 138 - 01160 OM 178 - 01082 OM 178 - 00765	2 - STAGE ISO 4414		DN	8 mm