



Cut protection

KRYTECH 809

Low risk - ISO B



CUT PROTECTION
LEVEL B



CATEGORY 2



ISO 13997:
9.5 N

DEXTERITY

EN ISO 21420:
5/5



Level B cut resistant gloves with crotch reinforcement. Enhanced durability combined with a high suppleness thanks to the HDPE liner. Touchscreen ability.

SPECIFIC ADVANTAGES



Comfort

- Added comfort and flexibility
- Ergonomic to reduce fatigue in the hand



Durability

- Suitable for long-term wear : excellent abrasion resistance
- A reinforced crotch in nitrile for an improved durability for the most exposed areas



Skin protection

- Contains traces of DMF in compliance with occupational exposure limits
- Free of harmful substances: OEKO-TEX® STANDARD 100



Suitable for touchscreen

- Can be used with touch devices & touch screen (thumb & index)



Washability

- Washable up to 5 times at 40°C , allowing to extend glove lifespan, reduce costs and waste.



Care for the environment

- Optimised individual packaging to limit plastic waste

INDUSTRIES

- Automotive/mechanical industry
- Aeronautics industry
- Construction Industry (Carpenters/Joiners)
- Construction Industry (Roofers/Tilers/Glazers)
- Construction Industry (Heating engineers/Plumbers)
- Construction Industry (Metalworkers/Locksmiths)
- Transport, logistics
- Paper industry
- Industrial equipment / Metal transformation
- White appliance

APPLICATIONS

- Installing steel structures
- Assembly
- Laying tiles, inserts, frames or zinc sheeting
- Handling metal parts
- Precision assembly
- Mechanical maintenance
- Maintenance
- Goods Handling on loading bays, docks, warehousing, etc.
- Handling cardboard and paper
- Goods handling on loading bays, docks, warehousing etc.




Cut protection

KRYTECH 809

Low risk - ISO B

LEGENDS



PRODUCT DETAILS

Interior finish	Seamless textile support from HDPE fibres
Gauge	13
Exterior finish	Ventilated back
Material	Polyurethane
Cuff characteristic	Knitted Cuff
Colour.s	Black
Length (cm)	21-27
European sizes	5 6 7 8 9 10 11

LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/bag 48 pairs/carton
-----------	---

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/01/22/0144
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE