



ENGLISH

Datasheet

RS Pro XENON 3000 STROBE

Stock No: 134-6750



Description

Light intense, compact stroboscope for stationary and mobile use. The large, homogeneous illumination surface delivers superb results even in difficult light conditions, making the RS STROBE 3000 XENON suitable for a very wide range of measurement, observation and inspection functions. It is especially suitable for demanding applications, such as those in the printing industry.

High illumination intensity (up to 10 Mega-lux) and extremely short flash duration ensure a precise sharply defined image however fast the movements are.

Suitable for web widths up to 300 mm, for web widths > 300 mm strobes can be connected in parallel.

Features

Exceptional light intensity
High image definition
Wide range of application options
Homogenous illumination area
External trigger facility

Technical Short Data

Frequency range: 0 ... 12,500 FPM
Light intensity max.: 500 LUX @ 30 cm
Illumination area: 20 x 30 cm
Dimensions: 150 x 130 x 112 mm

Scope of delivery

Stroboscope RS STROBE 3000 XENON
Operating instructions
1 DIN plug 5-pin for trigger input and/or power

Optional accessories

Strobe controller (RS part number 1346754)
Tripod (RS part number 1346765)
Articulating mounting arm (RS part number 1346764)
Eco Strobe controller (RS part number 1346755)
Mounting Kit (RS part number 1346763)
Connection cable (RS part number 1346766)
Extension cable (RS part number 1346767)
Strobe din plug (RS part number 1346762)