



Fuse-link, low voltage, 20A, AC 415 V, BS88/F2, 18 x 59 mm, gM, BS, 20M25

Catalog No. NSD20M25

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Motor current rating	I	A	32M63
Rated voltage			AC 415 V
Construction size			BS88/F2
Size			18 x 59 mm
Utilization category			gM
Description			motor-rated
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			offset bladed tags
Material			Ceramic body
Standards/Regulations			BS88-2 IEC 60269-2
Optional accessories			fuse-holder 32NNS and SC32

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	20
Rated voltage		V	415
Voltage type			AC
Rated switching capacity		kA	80
Utilization category			Other
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusmann.com/pdf/f1780856-8d9e-4fab-8cc8-1b803cf5c0d0.pdf
-------------------------	---