

**11-425** Designed to make the selection of hand protection easy

#### Previously known as: Puretough™P5000



# For any industry, the HyFlex indicator system helps the wearer to select the right protection for the job

- The smart combination of abrasion and cut resistance. Provides not only the protection needed in dry and slightly oily environments, but also educates workers to understand risk levels.
- Designed to make the selection of hand protection easy. The indicator system on these HyFlex gloves simplifies the selection of the right glove for the job for increased worker safety.
- The colour indicator system on the glove ensures the wearer of always having the appropriate cut level performance.



#### Industries

- Automotive
- Chemical

#### Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Applying sealers, touching up
- Production line support & maintenance
- Loading and unloading trucks and vehicles
- Product shipping, transport and delivery
- Maintenance
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Lock smith





# 11-425 Designed to make the selection of hand protection easy

**Technologies** 

DMF

### Previously known as: Puretough™P5000

**Cut Resistance Technology** 

## **Key Features**

- Water-based process is environmentally friendly, and has an innovative coating
- DMF-free
- Excellent abrasion resistance
- 11-425 is a seamless knitted glove, made with INTERCEPT technology
- Also available in vend pack

#### **Vulcanization Chemical Accelerators**

- Natural rubber proteins (in knitwrist elastic)
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

#### **Performance Standards & Regulatory Compliance**

#### **REACH Compliant**



# **Specifications**

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
-	Finishing: Palm Coated Coating Material: Water-Based polyurethane and nitrile Liner Material: Polyamide, Fiber glass, HPPE Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	225-270 mm; 8.86-10.62 inches	Grey	<ul> <li>12 pairs in a bag, 12 bags in a carton</li> </ul>

#### For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region Ansell Healthcare Europe NV Ansell Healthcare Europ Riverside Business Park Blvd International, 55 1070 Brussels, Belgium T: +32 (0) 2 528 74 00 F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Elva. Bernardo Quintana No. 700 Q7001 Torre II. Suites 1304, 1305 y 1306. Col. Centro Sur, c.p. 76079 Queretaro, Qro. Mexico T: +52 442 248 1544 / 248 3133

Ansell Commercial Mexico S.A. de C.V. Blvd. Bernardo Quintana No. 7001-C,

#### Canada

Ansell Canada 105 Lauder Cowansville, QC J2K 2K8 Canada T: +1 800 363 8340 F: +1 800 267 3551

North America Region

111 Wood Avenue South, Suite 210 Iselin, NJ 08830, USA T: +1 800 800 0444 F: +1 800 800 0445

Ansell Healthcare Products LLC

### Australia Ansell Limited

Ansell Limited Level 3,678 Victoria Street, Richmond, Vic, 3121 Australia T: +61 1800 337 041 F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center Ansell Global Trading Center (Malaysia) Sdn Bhd Prima 6, Prima Avenue Block 3512, Jalan Teknokrat 6 T: +603 8310 6688 F: +603 8310 6699

Ansell, <sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

