

Main

Range	Mureva
Product or component type	Case
Colour tint	Grey





Complementary

Plug, socket material	Self-extinguishing engineering polymer
Cover type	Hinged and gasketed cover
Device mounting	Panel mounting
Mounting mode	Panel-mounted
Fixing mode	4 fixing points
Base dimension	65 x 85 mm
Height	85 mm
Width	65 mm
IP degree of protection	IP65
IK degree of protection	IK09

Environment

IP degree of protection	IP65
IK degree of protection	IK09
Fire resistance	850 °C

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes