

FEATURES

- Energy-efficient portable infrared heater
- Up-to 95% efficient
- Dual infrared heating panels with individual switches
- Maximum heat output: 3kW
- Wheel-mounted
- Carrying handle
- Operating Voltage: 240 Vac and fitted with a mains cord terminated with a
- Type G UK plug
- Height 890mm; width 460mm; depth 300mm (with legs, 460mm deep)
- Weight: 14kg

3kW Infrared Heater, Portable, Type G - British 3-pin

RS Stock No.: 839-5252



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO brand, the Hotspot is a portable halogen infrared radiant quartz heater. Able to be rolled on wheels, the portable space heater can be positioned wherever there is an appropriate electrical outlet. The Hotspot is lightweight and fitted with both a carry handle and mounted on castors that are positioned to prevent tip-over.

General Specifications

Heat Type	Infrared
Control Type	On/Off Switch
Power Settings	2
Applications	Automobile workshop, Construction area, Assembly operation, Food and beverage, Storeroom and workshop, Greenhouse

Electrical Specifications

Maximum Output Power	3kW
Voltage Rating	240V
Nominal Current	10A
Frequency	50Hz
Plug Type	Type G - British 3-pin
Cord Length	1.8 metre cable (approx.)

Mechanical Specifications

Mounting	Portable
Dimensions	917mm x 421mm x 171mm
Height	917mm
Width	421mm
Depth	171mm
Weight	14kg

Approvals

Compliance/Certifications	RoHS
----------------------------------	------



