

## FEATURES

- Arbour press
- 2 ton output pressure
- Heavy casting
- Steel pinions and rams
- Height of 18 in
- Maximum work height of 7.5 in
- Length of 17 in
- Width of 7 in
- Throat depth of 5.5 in
- Weight of 37.5 kg
- Conforms to ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007 Electrostatic Control Standards

## RS PRO 2t Arbour Press

RS Stock No.: 713-3797



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

To take on small tasks such as staking, riveting, and similar press-fit work, you'll need a heavy-duty arbour press like this one from RS PRO. This precision-made machine press offers a rotating 4-position anvil for four different sizes of cut-out.

### General Specifications

<b>Type</b>	Arbour Press
<b>Output Pressure</b>	2t
<b>Body</b>	Heavy casting
<b>Rod Material</b>	Steel pinions
<b>Throat Depth</b>	5 ½ in
<b>Application</b>	Staking, riveting, installing, configuring and removing bearings and other press fit work.

### Mechanical Specifications

<b>Height</b>	18in
<b>Base Length</b>	17in
<b>Base Width</b>	7in
<b>Weight</b>	37.5kg

### Approvals

<b>Compliance/Certifications</b>	ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007
----------------------------------	---



Tons	Press Height	Max Work Height	Length	Width	Throat Depth	Weight Kg	RS Stock No
½	10 ½ in	4 in	9 ½ in	4 in	3 ¼ in	9.5	713-3784
1	13 in	4 ¾ in	10 ½ in	5 ¼ in	4	15.5	713-3788
2	18 in	7 ½ in	17 in	7 in	5 ½ in	37.5	713-3797