

tesa® 53398

Clean removal high strength mono filament tape

tesa® 53398 is a high-strength, polyester backed, fiberglass reinforced mono filament tape.

tesa® 53398 has a high tack and high shear resistant adhesive system. It has excellent aging properties and assures clean removal from many substrates.

Main Application

- Securing of metal coils for end-tapping
- Splicing of metal coils for processing
- Bundling and reinforcement of heavy goods, e.g. metal pipes

Technical Data

▪ Backing material	glassfibre / PET film	▪ Adhesion to steel	6 N/cm
▪ Total thickness	195 µm	▪ Elongation at break below	6 %
▪ Type of adhesive	synthetic rubber	▪ Tensile strength	800 N/cm

For latest information on this product please visit <http://l.tesa.com/?ip=53398>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.