

TEMPO TA201610



Sample photo

Order symbol: TA201610
Product nbr: 5814001
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074060730
El. number:
Finland: 3435684
Denmark: 8212035027
Sweden: 5814001
Norway:

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Dimensions:		Length	Width	Height	Rating:
mm:		201	163	98	Ingress Protection (EN 60529): IP 65
inch:		7.9	6.4	3.9	Impact Resistance (EN 62262): IK 07
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:		Polyamide			Certificates:
Cover screws colour:		Grey			Fimko
Gasket material:		PUR			Gost R
Temperatures:					
Short term:		-40 ... 80 °C			
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
MP 2016		Mounting plate			
DH-3		DIN-35 Mounting rail			
ARH 2320		DIN-35 Mounting rail			
FP 10674		Wall fastening lug (2 pcs) incl. screws			
DPS 14553		Grey sealing plug set			

