



# Product data sheet

Power tools for trade & industry

Cordless Circular Saw

## PRO GKS 18V-68



Cordless flexibility with corded power – for high performance

### The most important data

|                    |                   |
|--------------------|-------------------|
| Battery voltage    | 18.0 V            |
| Saw blade diameter | 190 mm            |
| No-load speed      | 5,000 – 5,000 rpm |

**Part Number** 0 601 6C9 001

## Technical data

### Technical data

|                                                |                    |
|------------------------------------------------|--------------------|
| No-load speed                                  | 5,000 – 5,000 rpm  |
| Saw blade diameter                             | 190 mm             |
| Saw blade bore diameter                        | 30 mm              |
| Battery voltage                                | 18.0 V             |
| Packaging dimensions (width x length x height) | 360 x 444 x 254 mm |

## Noise/vibration information

### Wood sawing

|                             |                      |
|-----------------------------|----------------------|
| Vibration emission value ah | 2.5 m/s <sup>2</sup> |
| Uncertainty K               | 1.5 m/s <sup>2</sup> |

**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

## Advantages:

- Maximum cordless cutting performance, fully equal to corded 1,800 W due to new BITURBO Brushless technology Outstanding ergonomics, due to a new auxiliary handle concept which ensures perfect control in all cutting positions Best cutting capacity in class with up to 70 mm cutting depth in 90° cuts

**BITURBO**  
BRUSHLESS**PROFESSIONAL**  
**18V**  
**SYSTEM**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

