


3216 Adaptors, machine operated

DIN 7428/ISO 3317, with outside hexagon for power operated IMPACT sockets DIN 3129/ISO 2725-2 with inside square DIN 3121/ISO 1174-2. Large collar diameter for better support of IMPACT sockets. Square drive with spring loaded locking pin, Chrome Alloy Steel, gunmetal finish.



Code	No	outside ■	"	outside ●	"	L mm	d mm	ΔΔ g	
32160001	3216/1	E 10	3/8	E 6.3	1/4	50	15.5	23	5
32160002	3216/2*	E 10	3/8	E 6.3	1/4	100	15.5	42	5

outside ■ DIN 3121/ISO 1174-2 Type E (spring-loaded locking pin)


outside ● DIN 3126/ISO 1173 Type E

* to be discontinued

3316/1 Adaptor, machine operated



DIN 7428/ISO 3317, with outside hexagon for power operated IMPACT sockets DIN 3129/ISO 2725-2 with inside square DIN 3121/ISO 1174-2. Large collar diameter for better support of IMPACT sockets. Square drive with spring loaded locking pin, Chrome Alloy Steel, gunmetal finish.



Code	No	outside ■	"	outside ●	"	L mm	d mm	ΔΔ g	
33160001		E 12.5	1/2	E 6.3	1/4	50	18	34	5

outside ■ DIN 3121/ISO 1174-2 Type E (spring-loaded locking pin)

outside ● DIN 3126/ISO 1173 Type E

BIT holder

square drive socket, for hand use only, for BITS-Screwdriver bits with outside hexagon 1/4" or 5/16" DIN 3126/ISO 1173 C 6.3 or C 8, Chrome Alloy Steel, chrome plated.

Internal hex drive with a collar-thrust spring (registered design).

Bits are easy to insert, lock securely in position and can be removed just as easily; even hex bits with a wide groove (Type E, DIN 3126/ISO 1173).



Code	No	inside ○	"	inside ○	"	d mm	L mm	ΔΔ g	
11180010	412	D 6.3	1/4	C 6.3	1/4	11.6	25	15	5
12180026	442	D 6.3	1/4	C 10	3/8	16.5	32	30	5
12180030	443	D 8	5/16	C 10	3/8	16.5	32	39	5
13180010	543	D 8	5/16	C 12.5	1/2	22	38	65	5

inside ○ DIN 3126/ISO 1173

inside ● DIN 3120/ISO 1174-1

412-1 BIT holder

○ 1/4" inside hexagon, DIN 3126/ISO 1173 D 6.3.

Outer ● 10 mm for use in tools with 10 mm internal hex drive or internal double hexagon (e.g. "FLEXI" double-ended flexi-joint spanners, T-handle universal joint spanners, box spanners, ratchet ring spanners etc.). Internal hex drive with a collar-thrust spring (registered design).

Bits are easy to insert, lock securely in position and can be removed just as easily; even hex bits with a wide groove (Type E, DIN 3126/ISO 1173).




Code	outside ●	L mm	d mm	ΔΔ g	
11180020	10 mm	20	11.6	11	5

736 BIT holder insert tools

Internal hex drive with a collar-thrust spring (registered design).

Bits are easy to insert, lock securely in position and can be removed just as easily; even hex bits with a wide groove (Type E, DIN 3126/ISO 1173).



Code	size	inside ○	"		b mm	h mm	S mm	ΔΔ g
58261010	10	D 8	5/16	9 x 12	16	12.5	17.5	47
58262610	10-1	D 6.3	1/4	9 x 12	14	10	17.5	45
58261040	40	D 8	5/16	14 x 18	16	12.5	25	112


inside ○ DIN 3126/ISO 1173

BITS screwdrivers

with outside hexagon DIN 3126/ISO 1173, Type E 6.3 (1/4"), for use in power drivers.

⊖ BITS screwdrivers

DIN 3127/ISO 2351, for slotted screws.



Code	No	a x b mm	outside ●	"	L mm	ΔΔ g	
08300635	1242	0.6 x 3.5	E 6.3	1/4	50	8	10
08300840	1244	0.8 x 4.0	E 6.3	1/4	50	9	10
08301055	1246	1.0 x 5.5	E 6.3	1/4	50	10	10
08301265	1248	1.2 x 6.5	E 6.3	1/4	50	12	10
08301680	1250	1.6 x 8.0	E 6.3	1/4	50	14	10

outside ● DIN 3126/ISO 1173

⊕ BITS screwdrivers

DIN 3128, for Phillips screws.



Code	No	Phillips-Recess®	outside ●	"	L mm	ΔΔ g	
08310001	1260	1	E 6.3	1/4	50	10	10
08310002	1261	2	E 6.3	1/4	50	11	10
08310003	1262	3	E 6.3	1/4	50	11	10

outside ● DIN 3126/ISO 1173

Phillips-Recess® DIN 5260

Adaptors

with outside hexagon,
for IMPACT screwdriver No 4030.



Code	No	outside ●"	outside ■"	L mm	△△ g	
32210001	4035	3/8	3/8	38	34	1
33210001	4036	3/8	1/2	38	43	1

⊖ BITS screwdrivers

for slotted screws,
for IMPACT driver No 4030.



Code	No	a x b mm	outside ●"	L mm	△△ g	
08400010	4040	1.0 x 7	3/8	40	17	10
08400014	4041	1.4 x 9	3/8	40	19	10
08400016	4042	1.6 x 10	3/8	40	21	10
08400020	4043	2.0 x 12	3/8	40	20	10
08400015	4044	1.5 x 13	3/8	40	24	10
08400025	4045	2.5 x 16	3/8	40	30	10

⊕ BITS screwdrivers

for Phillips screws,
for IMPACT driver No 4030.



Code	No	Phillips- Recess®	outside ●"	L mm	△△ g	
08410002	4050	2	3/8	35	17	10
08410003	4051	3	3/8	35	17	10
08410004	4052	4	3/8	35	17	10

Phillips-Recess® DIN 5260

⊙ BITS screwdrivers

for socket head screws,
for IMPACT driver No 4030.



Code	No	⊙ mm	outside ●"	L mm	△△ g	
08420005	4055	5	3/8	35	16	10
08420006	4056	6	3/8	35	16	10
08420008	4057	8	3/8	35	19	10
08420010	4058	10	3/8	35	23	10

