



PW3 WORK TROUSERS

DESCRIPTION

The PW3 Work Trouser with its smooth lines and stylish cut offers superb working comfort. It offers an impressive range of pockets including double rule pocket and pre-shaped, top loading knee pad pockets. Premium features incorporate crotch gusset, hammer loop and reinforced panels for extra durability. With adjustable leg length for added convenience the Urban Trouser is the smart choice for the modern workplace.

COMPOSITION

-  **Titanmill Plus: 65% Polyester, 35% Cotton, 300g**
-  **100% Polyester 600D Fabric, 210g**
-  **Zoom Grey/Black 28-48**

FEATURES

- Durable polycotton fabric for high performance and maximum wearer comfort
- Reflective piping for increased visibility
- Gripper elasticated inner waistline helping keep upper body garments in place
- Top-loading knee pad pockets for quick and easy access
- Free pair of kneepads included with this trouser
- 10 pockets for ample storage
- 2 Side pockets
- 2 back pockets with one open and one featuring a flap
- 1 Rule pocket
- 1 Spanner pocket
- 1 Pen pocket
- 1 Cargo pocket

STANDARDS

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
T601ZBR	ZOOM	28-14

FEATURES



HALF ELASTICATED WAIST
Half elasticated waist for a secure and comfortable fit



MACHINE WASHABLE AT 60°C
Reusable and machine washable at 60 degrees



UPF 40+
40+ UPF rated fabric to block 98% of UV rays



PERFORMANCE WORKWEAR
PW3™ contemporary workwear blends sports and lifestyle trends with function, a modern fit and improved comfort.

GET THE
COLLECTION

TECHINCAL INFORMATION



OEKO-TEX certification
13.HCN.29764

- Wash garment inside out
- Wash garment inside out and fully fastened
- Wash with similar colours
- Wash dark colours separately

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
T601ZBR28	Zoom Grey/Black	65	45	36	.904	5850.000	5036108291434	15036108781604
T601ZBR30	Zoom Grey/Black	65	45	36	.874	5850.000	5036108289899	15036108780119
T601ZBR32	Zoom Grey/Black	65	45	36	.938	5850.000	5036108289905	15036108780126
T601ZBR33	Zoom Grey/Black	65	45	36	.905	5850.000	5036108297450	15036108787217
T601ZBR34	Zoom Grey/Black	65	45	36	.921	5850.000	5036108289912	15036108780133
T601ZBR36	Zoom Grey/Black	65	45	36	.982	5850.000	5036108289929	15036108780140
T601ZBR38	Zoom Grey/Black	65	45	36	1.030	5850.000	5036108289936	15036108780157
T601ZBR40	Zoom Grey/Black	65	45	36	1.050	5850.000	5036108289943	15036108780164
T601ZBR41	Zoom Grey/Black	65	45	36	1.060	5850.000	5036108297467	15036108787224
T601ZBR42	Zoom Grey/Black	65	45	36	.994	5850.000	5036108289950	15036108780171
T601ZBR44	Zoom Grey/Black	65	45	36	1.000	5850.000	5036108291441	15036108781611
T601ZBR46	Zoom Grey/Black	65	45	36	1.020	5850.000	5036108291458	15036108781628
T601ZBR48	Zoom Grey/Black	65	45	36	1.100	5850.000	5036108291465	15036108781635