



9007FA3

LIMIT SWITCH LEVER ARM AW+C +OPTIONS



[Download your 9007FA3 datasheet](#)



[Characteristics](#) | Documents & Downloads

Main Hide

| | |
|------------------------------------|--|
| Range of product | 9007 |
| Series name | Heavy duty |
| Product or component type | Limit switch lever |
| Device short name | 9007C |
| Associated head | 9007A 9007B 9007C 9007N 9007T10 9007T5 |
| Associated complete product | 9007AW 9007C |
| Movement of operating head | Rotary |
| Type of operator | Steel spring return spring rod lever length: 12 in - offset: - - |
| Type of approach | Lateral approach |
| Positive opening | Without |

Complementary Hide

| | |
|-------------------------|--------------------|
| Switch actuation | By any moving part |
| Product weight | 0.1 lb(US) |

Environment Hide

| | |
|--|----------------------|
| Ambient air temperature for operation | -20...185 °F |
| Ambient air temperature for storage | -20...185 °F |
| Environmental characteristic | Standard environment |

Offer Sustainability Hide

| | |
|---|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1150 - Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold |
| Product environmental profile | Available download Product environmental |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty Hide

| | |
|---------------|-----------|
| Period | 18 months |
|---------------|-----------|

