



Main

Product range	Mureva BOX
Product type	Junction box
Colour	Grey (RAL 7035)
Quantity per package	5 pieces

Complementary

Mounting	Surface
Cable entry	Grommets
Fixing mode	Clip-on: cover
Interior dimensions	105 x 65 x 55 mm
Number of cable entries	8 diameter: 20 mm
Material	ABS (acrylonitrile butadiene-styrene): body PP (polypropylene): cover SBS (styrene butadiene styrene): grommet
Electrical insulation class	Class II conforming to IEC 536
Height	61 mm
Width	125 mm
Depth	83 mm
Net weight	0.092 kg

Environment

Operating temperature	-25...40 °C
IK-Class	IP55 conforming to IEC 60529
IK-Class	IK07 conforming to EN 50102
Glow wire temperature	650 °C
Standards	EN 60670 CE

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile