



### Main

Range	Resi9
Product name	Resi9 XE TL
Product or component type	Impulse relay
Device application	Remote control
Protection device type	1 x miniature circuit breaker (MCB) - 1P + N - 10 A - 230 V - C curve - 3000 A
Poles description	1P + N
Pole contact composition	1 NO
Network type	AC
Standards	EN/IEC 60669-1 EN/IEC 60669-2-2
Product certifications	NF


### Complementary

[In] rated current	10 A
Network frequency	50 Hz
[Ue] rated operational voltage	250 V AC 50 Hz
Control type	Remote and manual control
Technology type	Electromechanical
Control signal type	Impulse
Switching frequency	5 switching operation/minute
Impulse duration	50 ms
Remote control type	Illuminated push-button 3 mA
Local signalling	ON/OFF indication
[Uc] control circuit voltage	230 V AC 50 Hz
Supply inrush power	19 VA
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4
Height	86 mm
Width	36 mm
Depth	87 mm
Colour	White (RAL 9003)
Connections - terminals	Plug in, top Tunnel type terminals, top or bottom for 2 flexible wire(s) 0.5...1.5 mm <sup>2</sup> Tunnel type terminals, top or bottom for 2 flexible with ferrule wire(s) 0.5...1.5 mm <sup>2</sup> Tunnel type terminals, top or bottom for 2 rigid wire(s) 0.5...1.5 mm <sup>2</sup>
Market segment	Residential

### Environment

IP degree of protection	IP20
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins