

Geocel® JOINERS MATE MITRE BOND

TWO PART PROFESSIONAL INSTANT BONDING SYSTEM

Geocel® **Joiners Mate Mitre Bond** is a two part professional instant bonding system comprising of an adhesive and aerosol activator.

It is simple to use and bonds in 10 seconds. Geocel® **Joiners Mate Mitre Bond** is ideal for use on all cornice and profile mitres, trims, picture frames, skirting and architrave joints, worktop end strips, PVCu trims and much more.

Suitable for bonding: -

- MDF
- Wood
- Rubber
- PVCu
- Metal
- Most Plastics



TECHNICAL DATA

Storage Life	Approx 12 months when stored in a cool, frost free place, less once opened. Store away from direct sunlight.
Density	1300 -1700 at 25°C
Viscosity	1400-1700 mPa.s
Solids Content	100%
Drying Time	10 seconds
Colour	Clear
Temperature Resistance	-60°C to +80°C

Specification writers: These values are not intended for use in preparing specifications. Please contact your local **Geocel® Sales Representative** prior to writing specifications on this product.

APPLICATION

The surfaces to be glued should be clean, free from dust, grease and TOTALLY DRY. Ensure surfaces are close fitting. Spray activator onto one surface only and allow to evaporate. Apply adhesive onto the other surface. Assemble and hold for 10 seconds, curing will be almost instantaneous so exercise care when aligning.

Do not use externally on PVCu when moisture is present in the atmosphere or the PVCu is not totally dry. Contact with moisture during application can cause discolouration of the PVCu. This product is not suitable for permanent glass bonding or applications where the bonded joint may be immersed in water.

PACKAGING

Geocel® Joiners Mate Mitre Bond is supplied in a kit comprising of 50g adhesive and 200ml activator packed in boxes of 12.

HEALTH AND SAFETY

Health and Safety data sheets available on request. **CAUTION:** Adhesive, bonds skin and eyes in seconds, always read the label and consult health and safety information.

TECHNICAL SERVICE

For further technical information, advice on suitability for specific applications, or detailed Health and Safety information, contact **Geocel® Technical Service**.

IMPORTANT NOTE The information contained herein is offered in good faith and is believed to be accurate. However, because conditions and methods of use of our products are beyond our control, this information should not be used in substitution for customer's tests to ensure that Geocel's products are safe, effective and fully satisfactory for the intended end use. Suggestions of use shall not be taken as inducements to infringe any patent.

Geocel's sole warranty is that the product will meet the Geocel sales specifications in effect at the time of shipment.

Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted.

Geocel specifically disclaims any other express or implied warranty of fitness for a particular purpose or merchantability.

Geocel disclaims liability for any incidental or consequential damage.

Geocel®

Geocel Limited

Western Wood Way, Langage Science Park, Plympton, Plymouth, Devon, PL7 5BG

TEL: 01752 334350 Fax: 01752 202065 Email: info@geocel.co.uk
LIMITATIONS www.geocel.co.uk